

Rittal – The System.

Faster – better – everywhere.



SV 9346.000

**NH In-line Fuse-Switch
Disconnector**

State: 2026-01-17 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9346.000 - NH In-line Fuse-Switch Disconnector



Features

Model No.	SV 9346.000
Material	Fiberglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Color	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
Supply includes	3 mounting hooks
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 50 mm Height: 400 mm
Connection of round conductors	2.5 - 95 mm ²
Suitable for busbars	Height: 5, 10 mm

Features

Number of poles	3-pole
Round conductor cross-section	2.5 - 95 mm ²
Packaging unit	1 pc(s).
Net weight	1.1
Gross weight	1.3
Copper weight (kg per piece)	0.75
Customs tariff number	85369095
EAN	4028177628748
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK
