
Rittal - The System.

Faster – better – everywhere.





RX 9360.008 RiLineX Board

State: 2025-11-02 (Source: rittal.com/ca-en)



RX 9360.008 - RiLineX Board

Complete board 800 A, 905 mm for 1,000-mm-wide enclosures.

Features

Model No.	RX 9360.008
Benefits	Time saving through complete digital product data Shorter mounting time thanks to pre-mounted complete board Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC Tested short circuit resistance up to max. 65 kA Contact hazard protection up to IP 2XB, can be upgraded to IP 3X Tested and certified according to IEC and UL Simple expansion and field alignment
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 E-Cu
Color	RAL 35745 RAL 9005
Supply includes	Including integrated busbars
Protection category IP to IEC 60 529	IP 2XB
Standards	IEC 61 439-1/-2 UL 508
Rated current max.	800 A
Rated current (UL)	800 A
Electrical UL ratings (SCCR)	65 kA - 600 V, RMS 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Center-to-center spacing of busbars	60 mm

© Rittal 2025

Features

Rated impulse withstand voltage	12 kV
Ulmp	
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated impulse withstand current	143 kA 143 kA (UL)
Rated short-time withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Busbar dimensions	30 mm x 10 mm
Number of poles	3-pole
Fundamental frequency	5060 Hz
Ambient humidity (non-condensing)	1090 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Dimensions	Width: 905 mm Height: 246 mm Depth: 49 mm
Packaging unit	1 pc(s).
Net weight	11.5
Gross weight	12.032
Copper weight (kg per piece)	7.224
Customs tariff number	85369010
EAN	4028177997417

© Rittal 2025 3

Features

EC001900	ETIM 9

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025