


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.068 RiLineX Board

State: 2026-04-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.068 - RiLineX Board

Complete board 800 A, 505 mm for 600 mm wide enclosures.



## Features

Model No.	RX 9360.068
Benefits	<ul style="list-style-type: none"><li>Time saving through complete digital product data</li><li>Shorter mounting time thanks to pre-mounted complete board</li><li>Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC</li><li>Tested short circuit resistance up to max. 65 kA</li><li>Contact hazard protection up to IP 2XB, can be upgraded to IP 3X</li><li>Tested and certified according to IEC and UL</li><li>Simple expansion and field alignment</li></ul>
Material	<ul style="list-style-type: none"><li>Polyamide (PA 6)</li><li>Fire behavior corresponding to UL 94</li><li>E-Cu</li></ul>
Color	<ul style="list-style-type: none"><li>RAL 35745</li><li>RAL 9005</li></ul>
Supply includes	Including integrated busbars
Protection category IP to IEC 60 529	IP 2XB
Standards	<ul style="list-style-type: none"><li>IEC 61 439-1/-2</li><li>UL 508</li></ul>
Rated current max.	800 A

# Features

Rated current (UL)	800 A
Electrical UL ratings (SCCR)	65 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Center-to-center spacing of busbars	60 mm
Rated impulse withstand voltage U <sub>Imp</sub>	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage U <sub>i</sub>	1,000 V AC 1,500 V DC
Rated impulse withstand current	143 kA 143 kA (UL)
Rated short-time withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Busbar dimensions	30 mm x 10 mm
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 505 mm Height: 246 mm Depth: 49.2 mm

# Features

---

Packaging unit	1 pc(s).
Net weight	6.2 kg
Gross weight	6.762 kg
Copper weight (kg per piece)	3.999
Customs tariff number	85369010
ETIM 9	EC001900
Product description	RX RiLineX board 800 A, 3-pole, incl. busbars E-Cu 30x10 mm, 60 mm busbar center distance, W: 505 mm

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration