


Rittal – The System.

Faster – better – everywhere.



RX 9360.200

RiLineX connection adapter

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.200 - RiLineX connection adapter

Connection adapter RiLineX busbar platform for snap-on mounting, push-in conductor connection. Semi-automatic adjustment of busbar thickness 5/10 mm.



Features

Model No.	RX 9360.200
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current (max.)	67 A
Rated current max.	76 A
Rated current of round conductor	76 A
Rated current round conductor (UL)	66 A
Electrical UL ratings (SCCR)	5 kA - 600 V, RMS, unprotected 35 kA - 480 V, circuit breaker max. 60 A, DIVQ/7 100 kA - 600 V, fuse class J max. 100 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm

Features

Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 239.2 mm Depth: 103.3 mm
Connection of round conductors	1.5 - 16 mm ²
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	800 V AC 800 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	8 kV
Rated insulation voltage U _i	800 V
Power loss max.	7 W
Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non- condensing)	10...90 %
For busbar thickness	1.5 - 16 mm
Packaging unit	4 pc(s).

Features

Net weight	1.2 kg
Gross weight	1.656 kg
PCF/VE (cradle-to-gate)	13.4
Customs tariff number	85369010
ETIM 9	EC001531
Product description	RX connection adapter 3-pole, WH: 27x240 mm, conductor connection max. 16 mm ²

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration