

Rittal – The System.

Faster – better – everywhere.



RX 9360.525

RiLineX CB component adaptor

State: 2025-08-30 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.525 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Model No.	RX 9360.525
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	3 terminal covers
Protection category IP to IEC 60 529	IP 2XB
Rated current max.	400 A
Rated current (UL)	400 A
Rated impulse withstand voltage UImp	12 kV

Features

Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
To fit manufacturer (model)	ABB (S5 400, S5, T5, XT5, FG400, FG630) Chint (NM8N-400, NM8N-630, NXM-400S, NXM-630S, NXMS-400, NXMS-630) Eaton (NZM3) Fuji Electric (BW400_-3) Hager (X630) Hyundai Electric (400AF, 400, 630AF) LS Electric (400AF, TS400, TS630) Mitsubishi (NF400-SW, NF630-SW) OEZ (BH630) Rockwell (140G-K0F3-D40, 140G-M0F3-D63) Schneider (NSX400, NSX630) Schrack (MC3) Siemens (3VA23, 3VA24) Terasaki (S400, E630, S630)
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C

Features

Dimensions	Width: 140 mm Height: 325 mm
Packaging unit	1 pc(s).
Net weight	4
Gross weight	4.298
Copper weight (kg per piece)	1.652
Customs tariff number	85369095
EAN	4028177997127
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------