

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB device adapter

State: 2026-05-13 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.612 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "universal" version with sliding nuts offers maximum flexibility for switch installation. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

Model No.	RX 9360.612
Version	universal
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 connection compartment covers
Protection category IP to IEC 60 529	IP 2XB
Rated impulse withstand voltage U _{Imp}	8 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage U _i	1,000 V

Features

Contamination level	3
Number of poles	3-pole
Cable outlet	Bottom
Cross-section	15 mm ² 6 mm ²
To fit manufacturer (model)	Easily find the right device adapter with our selection guide in the Downloads area.
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 108.7 mm Height: 251.4 mm Depth: 62.8 mm
Packaging unit	1 pc(s).
Net weight	1.472 kg
Gross weight	1.474 kg
Copper weight (kg per piece)	0.608
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX CB device adapter 250 A, 3-pole, version: Universal Fix, cable outlet at bottom, W: 105 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration
