

Rittal – The System.

Faster – better – everywhere.



RX 9360.710 RiLineX device adapter

State: 2025-12-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.710 - RiLineX device adapter

Component adapter 45 mm. Snap-on mounting of components.



Features

Model No.	RX 9360.710
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable AWG 14 - 2 (16 A - 100 A) Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 14
Rated current of round conductor	16 A
Rated current of round conductor (UL)	16 A
Electrical UL ratings (SCCR)	5 kA - 600 V, RMS 100 kA - 600 V, fuse class RK5 max. 30 A, JDDZ/7 65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7

Features

Cable outlet	Top
For bar systems with center-to-center spacing	60 mm
Length of connection cable	150 mm
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packaging unit	4 pc(s).
Net weight	1.2
Gross weight	1.35

Features

Copper weight (kg per piece)	0.108
Customs tariff number	85369095
EAN	4028177997035
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity