

# Rittal – The System.

Faster – better – everywhere.



## PK 9524.100

## PK Polycarbonate Housings

State: 2025-08-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9524.100 - PK Polycarbonate Housings without knockouts

Wall-mounted enclosure of fiberglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                    |  |
|------------------------------------|--|
| Model No.                          | PK 9524.100  |
| Version                            | PK housing with transparent cover  |
| Product description                | Use in ambient temperature range: -35°C...+80°C. The specified temperatures can be limited by the installed equipment.   |
| Material                           | Housing: Fiber-glass reinforced polycarbonate<br>Cover transparent: Polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polythene |
| Color                              | RAL 7035   |
| Supply includes                    | Housing with cover<br>Cover screws<br>Insulating bungs for wall mounting screws  |
| Protection category NEMA           | NEMA 4X  |
| Protection category IP to EN 60529 | IP 66  |
| IK code                            | IK08   |

# Features

|                             |  |
|-----------------------------|--|
| Dimensions                  | Width: 360 mm<br>Height: 254 mm<br>Depth: 165 mm |
| Operating temperature range | -35 °C...80 °C                                   |
| Base material               | Polycarbonate                                    |
| Packaging unit              | 1 pc(s).   |
| Net weight                  | 1.72   |
| Gross weight                | 1.92   |
| Customs tariff number       | 94037000   |
| EAN                         | 4028177139916                                    |
| ETIM 9                      | EC000261   |
| ECLASS 8.0                  | 27180101   |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | C-UL<br>DNV-GL<br>UL      |
| Explanations | Declaration of conformity |