Rittal – The System.

Faster – better – everywhere.





RX 9361.300 RiLineX connection adapter

State: 2025-12-09 (Source: rittal.com/ca-en)



RX 9361.300 - RiLineX connection adapter

Connection adapter RiLineX busbar platform. Suitable for double connection (bar). Freely selectable phase distance. Only suitable for 10 mm busbars.



Features

Model No.	RX 9361.300
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current of laminated copper bar	1,500 A
Rated current of laminated copper bar (UL)	1,380 A
Electrical UL ratings (SCCR)	52.5 kA - 600 V, RMS 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, fuse class L max. 2000 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to- center spacing	60 mm
Number of poles	1-pole
Suitable for busbar system	RiLineX RiLine60

© Rittal 2025 2

Features

Dimensions	Width: 72.3 mm Height: 119.4 mm Depth: 117.4 mm
Clamping area for laminated copper bars (W x H)	50 x 10 mm
Suitable for busbars	15 x 10 20 x 10 30 x 10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage Ulmp	12 kV
Rated insulation voltage	1,000 V
Protection category IP to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C55 °C
Storage temperature range	-25 °C75 °C
Ambient humidity (non-condensing)	1090 %
Packaging unit	1 pc(s).
Net weight	0.65
Gross weight	0.688
Customs tariff number	85369010
ETIM 9	EC001531

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025