

Rittal – The System.

Faster – better – everywhere.



SV 9635.383 Component Adapters

State: 2025-07-16 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.383 - Component Adapters 1-pole

For assembly of switchgear and protective devices.

Features

| | |
|------------------------------|--|
| Model No. | SV 9635.383 |
| Version | L3 |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide Fire behavior corresponding to UL 94 |
| Color | RAL 7035 |
| Note | Different adapter designs are required depending on the desired phase connection The technical data may vary for UL applications. |
| Rated current max. | 63 A |
| Rated operating voltage | 690 V (AC), 1~ |
| Number of poles | 1-pole |
| Connection cables (AWG) | AWG 8 |
| Length of connection cable | 100 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | Fixed |
| Dimensions | Width: 18 mm Height: 160 mm Depth: 35 mm |
| Packaging unit | 6 pc(s). |
| Net weight | 0.39 |
| Gross weight | 0.499 |
| Copper weight (kg per piece) | 0.026 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177934573 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |