## Rittal – The System.

Faster – better – everywhere.





# SV 9635.410 Motor control unit

State: 2025-11-29 (Source: rittal.com/ca-en)



## SV 9635.410 - Motor control unit 3-pole

For controlling motors as direct or reversing starter with integral overload protection.

#### **Features**

Model No.	SV 9635.410	
Function principle	For controlling motors as direct or reversing starter with integral overload protection  The hybrid technology used allows for frequent switching with no wear by means of semiconductors  During operation, mechanical contacts ensure low power loss  Space-saving design due to low structural width	
Material	Polyamide Fire protection corresponding to UL 94-V0	
Color	RAL 7035	
Power dissipation (max.)	5.5 W	
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz	
Rated current max.	2.4 A	
Note	The technical data may vary for UL applications.	
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm	
Connection of round conductors	0.14 - 2.5 mm²	
Adjustable current monitoring	0.18 - 2.4 A	
Packaging unit	1 pc(s).	
Net weight	0.38	
Gross weight	0.387	
Customs tariff number	85371091	
EAN	4028177817302	
ETIM 9	EC002572	

© Rittal 2025

### **Features**

8 8.0 27370804

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3