

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.215**

**RiLineX NH fuse switch  
disconnecter**

State: 2026-05-21 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.215 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in size 2 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M10 screw connection. Cable outlet can be individually converted at the top or bottom. Including electronic fuse monitoring.



## Features

|   |   |
|---|---|
| Model No.                                     | RX 9362.215   |
| Version                                       | For 60 mm busbar systems  |
| Benefits                                      | Cover, lockable and sealable<br>Voltage test through separate opening<br>Tool-free conversion of the cable outlet<br>Park position for simplified maintenance work<br>All variants also with electronic fuse monitoring |
| Material                                      | Polyamide (PA 6)<br>Fire behavior corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated  |
| Color   | RAL 9005<br>RAL 35745   |
| Supply includes                               | Incl. connection plug for electrical fuse monitoring  |
| For bar systems with center-to-center spacing | 60 mm   |
| Cable outlet                                  | Top/bottom  |
| Type of connection (electrical)               | Screw M10   |
| Fuse inserts                                  | NH 2  |

# Features

|                                      |  |
|--------------------------------------|--|
| Rated operating voltage              | 690 V AC   |
| For NH size                          | 2  |
| Test specification                   | IEC 60 947-3<br>IEC 60 269-2 (fuse inserts)  |
| Dimensions                           | Width: 208.5 mm<br>Height: 348.7 mm<br>Depth: 134.6 mm                                   |
| Operating temperature range          | -5 °C...35 °C  |
| Storage temperature range            | -25 °C...70 °C   |
| Suitable for busbars                 | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Suitable for busbar system           | RiLineX<br>RiLine60  |
| Number of poles                      | 3-pole   |
| Contamination level                  | 3  |
| With electronic fuse monitoring      | Yes  |
| Protection category IP to IEC 60 529 | IP 2XB   |
| Fire load                            | 46.16 MJ/m <sup>2</sup>  |
| Power loss max.                      | 98 W   |
| Packaging unit                       | 1 pc(s).   |
| Net weight                           | 4.2 kg   |
| Gross weight                         | 4.268 kg   |
| Copper weight (kg per piece)         | 1.75   |
| PCF/VE (cradle-to-gate)              | 28.53  |
| Customs tariff number                | 85369095   |
| ETIM 9                               | EC001040   |
| Product description                  | RX NH fuse-switch-connector size 2, 400 A, 3-pole, M10 screw, with fuse monitoring 800 V |

# Approvals

---

Approvals

CQC-CCC

---

Explanations

Declaration of conformity

PCF-declaration