

# Rittal – The System.

Faster – better – everywhere.



## VX 9666.966

## Baying-enclosure system VX25

State: 2025-07-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9666.966 - Baying-enclosure system VX25 Distribution enclosures

VX baying system used as a distribution enclosure and prepared for ISV expansion module.



## Features

Model No.	VX 9666.966
Material	Carbon steel
Surface finish	Enclosure frame: Dipcoat-primed Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Base Plates Rear panel Roof plate Lock: 3 mm double-bit
Number of doors	2
Note	Use VX basic enclosures for 600 mm wide installation divider For a base/plinth height of 200 mm, 2 packs each of plinth corner pieces, 100 mm and base/plinth trim panels, 100 mm are required

## Features

Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Test specification	IEC 61 439-1/-2
Dimensions	Width: 1,100 mm Height: 2,000 mm Depth: 400 mm
Packaging unit	1 pc(s).
Net weight	111.65
Gross weight	118.6
PCF/VE (cradle-to-gate)	359.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177929777
ETIM 9	EC000214
ECLASS 8.0	27142409

## Approvals

Approvals	Bureau Veritas DNV-GL
Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK