

Rittal – The System.

Faster – better – everywhere.



SV 9676.747 Connection Plate

State: 2025-09-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.747 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

Features

Model No.	SV 9676.747
Product description	For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., $\text{Length} = W + \text{fastening measurement}$. Screws are not included with the supply Busbar claw with threaded insert M10
Number of bars per conductor	2
Mounting dimensions	50 mm
Clamping area for laminated copper bars (W x H)	32 x 20 mm
Suitable for laminated copper bars	Qty.: 2 Number of lamina: 10 Lamina width: 32 mm Lamina thickness: 1 mm
Packaging unit	1 pc(s).
Net weight	0.34
Gross weight	0.346
Copper weight (kg per piece)	0.13
Customs tariff number	73269098
EAN	4028177625556
ETIM 9	EC002270

Features

ECLASS 8.0	27400613
------------	----------

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---