

Rittal – The System.

Faster – better – everywhere.



SV 9676.748 Connection Plate

State: 2024-06-03 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.748 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

Features

Model No.	SV 9676.748
Product description	For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., $\text{Length} = W + \text{fastening measurement}$. Screws are not included with the supply Busbar claw with threaded insert M10
Number of bars per conductor	2
Mounting dimensions	50 mm
Clamping area for laminated copper bars (W x H)	63 x 20 mm
Suitable for laminated copper bars	Qty.: 2 Number of lamina: 10 Lamina width: 63 mm Lamina thickness: 1 mm
Packaging unit	1 pc(s).
Weight/packaging unit	0.48 kg
Copper weight (kg per piece)	0.19
Customs tariff number	85369010
EAN	4028177625563
ETIM 7.0	EC001900
ECLASS 8.0	27400613

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK