

Rittal – The System.

Faster – better – everywhere.



SV 9676.749 Connection Plate

State: 2026-06-03 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.749 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

Features

| | |
|---|---|
| Model No. | SV 9676.749 |
| Product description | For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness. |
| Material | Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel |
| Supply includes | Assembly parts (excluding screws) |
| Mounting tip | The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply Busbar claw with threaded insert M10 |
| Rails per conductor | 2 |
| Mounting dimensions | 50 mm |
| Clamping area for laminated copper bars (W x H) | 100 x 20 mm |
| Suitable for laminated copper bars | Qty.: 2 Number of lamina: 10 Lamina width: 100 mm Lamina thickness: 1 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 0.62 kg |
| Gross weight | 0.639 kg |
| Copper weight (kg per piece) | 0.27 |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002270 |

Features

| | |
|---------------------|--|
| ECLASS 8.0 | 27400613 |
| Product description | SV Connection plate, clamping area WH: 100x20 mm, (Flat-PLS) |

Approvals

| | |
|--------------|------------------------------|
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |