Rittal - The System.

Faster – better – everywhere.





SV 9677.000 NH In-line Fuse-Switch <u>Disconnector</u>

State: 2025-10-30 (Source: rittal.com/ca-en)



SV 9677.000 - NH In-line Fuse-Switch Disconnector

3-pole, for busbar systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.000
Version	3-pole, switchable
Material	Polyamide
	Fire protection corresponding to UL 94-V0
	Contact tracks: Partially silver-plated hard copper
Color	Chassis: RAL 7035
	Cover: RAL 7001
	Handle: RAL 7016
For NH size	00
For bar systems with center-to- center spacing	185 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Number of poles	3-pole
Rated operating voltage	800 V (AC), 3~
Rated operating current max.	160 A
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Test specification	IEC 60 947-3
	IEC 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 50 mm
	Height: 670 mm
Connection of round conductors	1.5 - 95 mm²

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	2.44
Gross weight	2.66
Copper weight (kg per piece)	0.6
Customs tariff number	85365080
EAN	4028177705418
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3