

Rittal – The System.

Faster – better – everywhere.



SV 9677.770 Component Adapters

State: 2026-03-07 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.770 - Component Adapters Terminal fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

| | |
|---|--|
| Model No. | SV 9677.770 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Supply includes | Connection straps |
| For bar systems with center-to-center spacing | 185 mm |
| Cable outlet | Bottom |
| Installation type | Clamping attachment |
| Number of poles | 3-pole |
| Rated current max. | 630 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For mounting on busbar systems with or without cover section |
| Dimensions | Width: 150 mm Height: 585 mm |
| Suitable for busbars | Height: 10 mm |
| To fit manufacturer (model) | ABB (Tmax T5) Eaton (NZM3) Schneider Electric (NSX630) Siemens (3VA23, 3VA24, 3VL4) |
| Packaging unit | 1 pc(s). |
| Net weight | 6.2 kg |

Features

| | |
|------------------------------|---|
| Gross weight | 6.629 kg |
| Copper weight (kg per piece) | 3.754 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor, 630 A, 690 V, 3-pole, 185 mm, clamping attachment |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |