


# Rittal – The System.

Faster – better – everywhere.



## SV 9677.910

### Connection block

State: 2026-01-29 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

# SV 9677.910 - Connection block

For connecting cables and laminated copper bars.

## Features

Model No.	SV 9677.910
Product description	For connecting conductors or laminated copper bars.
Material	Carbon steel, zinc-plated E-Cu, tin-plated
Clamping area height	20 mm
Clamping area width	80 mm
Cable outlet	Top/bottom
Rated current max.	1,600 A
Dimensions	Width: 98 mm
Suitable for busbars	Height: 10 mm
Packaging unit	1 pc(s).
Net weight	0.9
Gross weight	0.982
Copper weight (kg per piece)	0.689
PCF/VE (cradle-to-gate)	3.7 kg CO <sub>2</sub> eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	85369095
EAN	4028177705302
ETIM 9	EC002270
ECLASS 8.0	27400613

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK