

Rittal – The System.

Faster – better – everywhere.



SV 9677.958 Current Transformers

State: 2025-07-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.958 - Current Transformers

For inductive measurement of current flow.

Features

Model No.	SV 9677.958
Product description	Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly.
Material	Polyamide
Suitable for Model No.	9677930
Rated output	2.5 VA
Type of connection (electrical)	Box terminal
Insulation material (class)	H
Primary current	800 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm ²
Rated frequency	50 - 60 Hz
Packaging unit	1 pc(s).
Net weight	0.16
Gross weight	0.17
Customs tariff number	85043129
EAN	4028177984424
ETIM 9	EC002048

Features

ECLASS 8.0

27141146