
Rittal – The System.

Faster – better – everywhere.





VX 9680.808 Baying-enclosure system VX25

State: 2025-10-31 (Source: rittal.com/ca-en)



VX 9680.808 - Baying-enclosure system VX25 Modular enclosure

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

Features

Model No. Material Surface finish	VX 9680.808 Carbon steel, 1.5 mm Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured
Surface finish	Rear panel: Dipcoat-primed, powder-coated on the outside, textured
	Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Rear panel Base Plates
Protection category IP to EN 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Packaging unit	1 pc(s).
Net weight	49.54
Gross weight	63.6
PCF/VE (cradle-to-gate)	158.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177929555

© Rittal 2025

Features

ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity UK

© Rittal 2025 3