

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.570 Current Transformers

State: 2026-06-09 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.570 - Current Transformers

## Features

Model No.	SV 9393.570
Version	Output voltage 333 mV
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 9005
Supply includes	2x mounting feet 4 insulating caps 2 primary bar clamps 4 threaded pins
Suitable for busbars	2 x 80 x 10 60 x 60
Primary current	2,000 A
Standards	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV Regulation 3
Dimensions	Width: 105 mm Height: 132 mm Depth: 30 mm
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Fundamental frequency	50...60 Hz
Accuracy Class	0.5
Insulation material (class)	F

# Features

---

Packaging unit	1 pc(s).
Net weight	0.435 kg
Gross weight	0.443 kg
Customs tariff number	85043129
ETIM 9	EC002048
Product description	SV Current transformer 2000 A, 70 mm

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------