

Rittal – The System.

Faster – better – everywhere.



SV 9635.100

Circuit-Breaker Component Adaptors

State: 2026-01-14 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9635.100 - Circuit-Breaker Component Adaptors 3-pole

For mechanical attachment and the direct contact of circuit breakers on the board.

Features

| | |
|--------------------------------|--|
| Model No. | SV 9635.100 |
| Function principle | For mechanical attachment and direct contact of circuit breakers on the board Mounting the circuit breaker with variably adjustable fastening points (M4) |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Note | When selecting the CB device adapter, pay attention to the mounting distance of the circuit breaker There may be a reduction in power depending on the circuit breaker used The technical data may vary for UL applications. |
| Rated current max. | 160 A |
| Rated operating voltage | 600 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Dimensions | Width: 90 mm Height: 160 mm Depth: 45 mm |
| Distance between fixing points | 25 mm |
| Cable outlet | Top/bottom |
| To fit manufacturer (model) | ABB (XT1) Allen Bradley (140G-G) Siemens (3VA10, 3VA11, 3VA51) |
| Packaging unit | 1 pc(s). |
| Net weight | 0.58 |

Features

| | |
|------------------------------|---------------|
| Gross weight | 0.582 |
| Copper weight (kg per piece) | 0.276 |
| Customs tariff number | 85369095 |
| EAN | 4028177951877 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
