

Rittal – The System.

Faster – better – everywhere.



SV 9635.700

NH Fuse-Switch Disconnectors


State: 2026-01-14 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

SV 9635.700 - NH Fuse-Switch Disconnectors Size 000

For RiLine Compact busbar system.



Features

Model No.	SV 9635.700
Function principle	To protect connected equipment Integrated test holes provide measurement access to the contact parts of the fuse inserts For the cable outlet at the top, the NH fuse switch disconnector must be rotated 180° when mounted on the board
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Color	RAL 7035
Test specification	IEC 60 947-3
For NH size	000
Rated operating current max.	125 A
Rated operating voltage	440 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal

Features

Connection of round conductors	2.5 - 50 mm ²
Clamping area for laminated copper bars (W x H)	10 x 10 mm
Dimensions	Width: 49.5 mm Height: 174.5 mm Depth: 96 mm
Packaging unit	1 pc(s).
Net weight	0.52
Gross weight	0.562
Copper weight (kg per piece)	0.145
Customs tariff number	85369095
EAN	4028177937604
ETIM 9	EC001040
ECLASS 8.0	27371401