

Rittal – The System.

Faster – better – everywhere.



SV 9676.730

Direct Connection Terminal

State: 2025-07-26 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9676.730 - Direct Connection Terminal for round conductor

For the direct connection of 95 – 300 mm² round conductors (single-wire and multi-wire).

Features

Model No.	SV 9676.730
Product description	For connecting round conductors to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connecting terminal: Brass, tin-plated Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply Busbar claw with threaded insert M10
Number of bars per conductor	2
Connection of round conductors	95 - 300 mm ²
Mounting dimensions	60 mm
Packaging unit	1 pc(s).
Net weight	0.32
Gross weight	0.327
Customs tariff number	85369010
EAN	4028177625549
ETIM 9	EC002270
ECLASS 8.0	27400613

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK