# Rittal - The System.

Faster – better – everywhere.





# SV 9677.340 NH In-line Fuse-Switch Disconnector

State: 2025-11-26 (Source: rittal.com/ca-en)



# SV 9677.340 - NH In-line Fuse-Switch Disconnector

3-pole, for busbar systems with 185 mm center-to-center distance.

### **Features**

Model No.	SV 9677.340
Version	3-pole, switchable
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Partially silver-plated hard copper
Color	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For NH size	3
For bar systems with center-to- center spacing	185 mm
Cable outlet	Bottom
Type of connection (electrical)	Bolt M12
Number of poles	3-pole
Rated operating voltage	690 V (AC), 3~
Rated operating current max.	1,250 A
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
For converter installation	Yes
Dimensions	Width: 200 mm Height: 670 mm
Connection of round conductors	6 - 240 mm²
Suitable for busbars	Height: 10 mm

© Rittal 2025

## **Features**

Double disconnector	Yes
Packaging unit	1 pc(s).
Net weight	14
Gross weight	14.4
Copper weight (kg per piece)	6.838
Customs tariff number	85365080
EAN	4028177705579
ETIM 9	EC001046
ECLASS 8.0	27371402

# Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3