

Rittal – The System.

Faster – better – everywhere.



SV 9677.715

Component Adapters

State: 2026-02-11 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.715 - Component Adapters Screw fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.715
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
For bar systems with center-to-center spacing	185 mm
Cable outlet	Bottom
Installation type	Screw attachment
Number of poles	3-pole
Rated current max.	1,600 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal for fastening to perforated busbars. Note that no cover sections are fitted in the vicinity of the device.
Dimensions	Width: 300 mm Height: 652 mm
Suitable for busbars	Height: 10 mm
To fit manufacturer (model)	ABB (Tmax T7 - 1250 A/1600 A) Eaton (NZM4 - 1250 A/1600 A) Schneider Electric (NS - 1250 A/1600 A) Siemens (3VA27 - 1250 A/1600 A)
Packaging unit	1 pc(s).
Net weight	19.34
Gross weight	21.4

Features

Copper weight (kg per piece) 14.749

Customs tariff number 85369095

EAN 4028177707061

ETIM 9 EC001531

ECLASS 8.0 27370304

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity
Declaration of conformity UK