

Rittal – The System.

Faster – better – everywhere.



SV 9677.952

Current Transformers

State: 2025-08-02 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.952 - Current Transformers

For inductive measurement of current flow.

Features

Model No.	SV 9677.952
Product description	Compact design without altering the installation depth via mechanical integration into the assembly components (185 mm center-to-center spacing); this allows space-saving assembly.
Material	Polyamide
For size	3
Suitable for Model No.	9677.360 9677.365 9677.380 9677.930
Rated output	1.5 VA
Type of connection (electrical)	Box terminal
Insulation material (class)	H
Primary current	500 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Connection of round conductors	2.5 - 4 mm ²
Rated frequency	50 - 60 Hz
Packaging unit	1 pc(s).
Net weight	0.136
Gross weight	0.146

Features

Customs tariff number	85043129
EAN	4028177984431
ETIM 9	EC002048
ECLASS 8.0	27141146