

Rittal – The System.

Faster – better – everywhere.



VX 9680.408

Baying-enclosure system VX25

State: 2026-01-16 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 9680.408 - Baying-enclosure system VX25 Modular enclosure

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

Features

Model No.	VX 9680.408
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Rear panel Base Plates
Protection category IP to EN 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/2 IEC 61 641
Dimensions	Width: 400 mm Height: 2,000 mm Depth: 800 mm
Packaging unit	1 pc(s).
Net weight	37.2
Gross weight	40.2
PCF/VE (cradle-to-gate)	113.3 kg CO ₂ eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
EAN	4028177929753

Features

ETIM 9 EC000261

ECLASS 8.0 27180101

Approvals

Certificates Surface finish

Explanations Declaration of conformity UK