

# Rittal – The System.

Faster – better – everywhere.



## VX 9680.628 Modular enclosure

State: 2026-07-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9680.628 - Modular enclosure Baying-enclosure system VX25

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | VX 9680.628   |
| Material                            | Carbon steel, 1.5 mm  |
| Surface finish                      | Enclosure frame: Dipcoat-primed<br>Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Base plates: Zinc-plated |
| Color                               | RAL 7035  |
| Supply includes                     | Enclosure frame<br>Rear panel<br>Base Plates  |
| Protection category IP to EN 60529  | Up to IP 54, depending on the panels  |
| Test specification                  | IEC 61 439-1/-2<br>IEC 61 641   |
| Dimensions                          | Width: 600 mm<br>Height: 2,200 mm<br>Depth: 800 mm  |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 47.25 kg  |
| Gross weight                        | 52.2 kg   |
| PCF/VE (cradle-to-gate)             | 137.5 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared                    |
| Customs tariff number               | 94032080  |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 9              | EC000261   |
| ECLASS 8.0          | 27180101   |
| Product description | VX Modular enclosure, WHdepth 600x2200x800 mm, sheet steel |

---

# Approvals

---

|              |                |
|--------------|----------------|
| Certificates | Surface finish |
|--------------|----------------|

---