

Rittal – The System.

Faster – better – everywhere.



SV 9685.725

Laminated copper busbar, tin-plated

State: 2026-06-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9685.725 - Laminated copper busbar, tin-plated

Cu lamina made from high-purity electrolytic copper F20, tin-plated, length: 2000 mm/bar.

Features

Model No.	SV 9685.725
Material	Cu lamina: High-purity electrolyte copper Insulation: Highly resistant vinyl blend, expansion 370%, temperature: -30°C ... +105°C, fire protection according to UL-94 V0, dielectric strength: 20 kV/mm
Length	2,000 mm
Rated current for temperature increase 50 K	770 A
Rated current for temperature increase 30 K	585 A
Rated current for temperature increase 70 K	920 A
Note	Assembly = number of layers x layer width x layer thickness May be cut to length as required The conductor temperature of the laminated copper bar is derived by adding the ambient temperature and the temperature increase together. Example: 3565.005 carrying 180 A, i.e. the temperature increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C.
Laminated flat copper version	Number of lamina: 10 Lamina width: 24 mm Lamina thickness: 1 mm
Packaging unit	1 pc(s).
Net weight	4.5 kg
Gross weight	5.005 kg
Copper weight (kg per piece)	4.27
Customs tariff number	85446010

Features

Product description

SV laminated copper busbar E-Cu tin-plated, WH: 24 x 10 mm, L: 2000 mm

Approvals

Approvals

UR + C-UR (recognized)