

# Rittal – The System.

Faster – better – everywhere.



## VX 9680.808

# Baying-enclosure system VX25

State: 2026-05-28 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9680.808 - Baying-enclosure system VX25 Modular enclosure

VX baying system for installation with partial doors and inner compartmentalization in a modular design.

## Features

Model No.	VX 9680.808
Material	Carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame Rear panel Base Plates
Protection category IP to EN 60529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Packaging unit	1 pc(s).
Net weight	49.54 kg
Gross weight	63.6 kg
PCF/VE (cradle-to-gate)	158.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080

# Features

---

ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	VX Modular enclosure, WHdepth 800x2000x800 mm, sheet steel

# Approvals

---

Certificates	Surface finish
Explanations	Declaration of conformity UK