

Rittal – The System.

Faster – better – everywhere.



CS 9751.912

Multifunction housing

State: 2025-12-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9751.912 - Multifunction housing

Double-walled housing for outdoor installation made of aluminum with resistance class RC2.



Features

Model No.	CS 9751.912
Product description	2-door, double-walled housing for outdoor installation made of aluminum with resistance class RC 2. Includes cable management base/plinth. Prepared to accept 19"/ETSI combination rails and a Direct Air Cooling System (DAC).
Material	Housing, roof, door(s), base plate: Aluminum, AlMg3, 2.0 mm Mounting plate(s): Aluminum, AlMg3, 3.0 mm Support rail: Stainless steel 1.4016 (AISI 430)
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Weather protection roof with ventilation, prepared for the installation of a Direct Air Cooling System (DAC) Door stay using mechanical system (approx. 155°) Swing lever handle and semi-cylinder, lock BJ20027 Cable routing base, planked all around Flange Plates Gland plate Including 2 mounting plates Screwed-in middle bar
Dimensions	Width: 1,300 mm Height: 1,050 mm Depth: 500 mm

Features

Dimensions	Overall height: 1,600 mm Rain canopy height: 130 mm Height of base/plinth: 400 mm
Dimensions of mounting plate (W x H)	610 mm x 941 mm 548 mm x 941 mm
Number of doors	2
Door opening angle	Approximately 155°
Lock	Lock version: 3-point locking system with single and double locking cylinder No. of locks: 2 Lock Insert: BJ20027
Gland plate	Size: 2 Qty.: 3
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
Note on Model No.:	Delivery times on request.
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	115
Gross weight	135
EAN	4028177980853
ETIM 9	EC000261