


# Rittal – The System.

Faster – better – everywhere.



## RX 9360.802

## RiLineX bus-mounting fuse base

状态: 2025-10-5 (来源: [rittal.com/cn-zh](http://rittal.com/cn-zh))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.802 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm<sup>2</sup> at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.



## 特征

型号	RX 9360.802
您的获益	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm <sup>2</sup> Complete contact hazard protection without any additional accessories (such as screw caps)
材料	聚酰胺 (PA 6) 防火性能符合 UL 94-V0
颜色	RAL 35745 RAL 9005

# 特征

供货范围	4 bus-mounting fuse bases 12 reducers for D 01 fuses
导线出线	下面
极数	3 极
适合于母线系统	RiLineX RiLine60
尺寸	宽度: 27 mm 高度: 263 mm 深度: 123.5 mm
圆导线连接, 细线带电缆芯线套管	1.5 - 16 mm <sup>2</sup>
连接圆导线, 细绞线, 带 AWG 冷压端头	AWG 16 - AWG 6
圆导线连接, 多芯	1.5 - 16 mm <sup>2</sup>
连接圆导线, 多股 (AWG 标准)	AWG 16 - AWG 6
适合于母线	高度: 5, 10 mm
适合于母线	15 x 5/10 20 x 5/10 30 x 5/10
额定电压	400 V AC
过压类别	4
污染等级	3
标准	IEC/DIN EN 60 947-3
Rated insulation voltage	1,000 V
Power dissipation (max.)	5.5 W
防护等级 IP, 符合 IEC 60 529 标准	IP 2XB

# 特征

Operation humidity max	90 %
工作温度范围	-5 °C...55 °C
贮存温度范围	-25 °C...75 °C
空气湿度（没有凝露）	10...90 %
Utilisation category	AC-21B (400 V/100 A)
保险器熔丝	D 02-E 18
包装单元	4 件
净重	1.432
毛重	1.437
铜成分（kg/件）	0.07
税率号	85369095
ETIM 9	EC001644

# 批准

解释	符合性声明
----	-------