

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.043

# Energy-saving enclosure

State: 2026-05-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9690.043 - Energy-saving enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fitting. Ideal for efficient and modular expansion of energy storage with slide rails.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SV 9690.043  |
| Version                             | With flexible interior fitting   |
| Material                            | Enclosure frame: Carbon steel, 1.5 mm<br>Roof sheet: carbon steel, 1.5 mm<br>Door: Carbon steel, 1.5 mm<br>Rear wall: carbon steel, 1.5 mm |
| Surface finish                      | Enclosure frame: Dipcoat-primed<br>Door, roof and rear panel: powder-coated, textured paint  |
| Color                               | RAL 7035   |
| Supply includes                     | Enclosure frame<br>Door and rear panel, perforated<br>Roof plate<br>Lock: 3 mm double-bit  |
| Protection category IP to EN 60 529 | IP 20  |
| Dimensions                          | Width: 800 mm<br>Height: 2,000 mm<br>Depth: 800 mm   |
| PCF/VE (cradle-to-gate)             | 290.48 kg CO2 eq (Cat B)   |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared                       |
| Customs tariff number               | 94032080   |
| ETIM 9                              | EC000261   |
| Product description                 | VX ESS energy storage enclosure WHD: 800x2,000x800 mm, with door, rear panel, interior fitting   |

# Approvals

---

Explanations

Declaration of conformity