

Rittal – The System.

Faster – better – everywhere.



CS 9782.828

CS Toptec, bayable

State: 2026-01-17 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9782.828 - CS Toptec, bayable

Bayable, double-walled outdoor housing with 100 mm base, door, rear panel, and seamlessly bayable weatherproof roof. The complete enclosure frame is available for efficient and flexible interior fitting. The housing is prepared for the installation of a wall-mounted cooling unit Blue e+ Outdoor.



Features

Model No.	CS 9782.828
Version	For baying With cut-out for outdoor climate control unit 6824.28 - 17060.71 BTU/h
Material	Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035

Features

Supply includes	Bayable, double-walled outdoor housing Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027 Rear panel Rain canopy Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Dimensions	Overall height: 2,145 mm Rain canopy height: 45 mm Height of base/plinth: 100 mm
Number of doors	1
Lock	Lock version: 4-point locking system No. of locks: 1 Lock Insert: BJ20027
Gland plate	Size: 2 Qty.: 2
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
IK code	IK10
Note	All enclosure panels are double wall and grounded (external wall to internal wall) For the assembly of an enclosure, side panels for CS Toptec, bayable are required
Note on Model No.:	A climate control unit is needed to seal the cut-out
Packaging unit	1 pc(s).
Net weight	82
Gross weight	92

Features

EAN	4028177986152
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Explanations	Declaration of conformity
--------------	---------------------------
