


# Rittal – The System.

Faster – better – everywhere.



## CS 9782.868 CS Toptec, bayable

State: 2026-05-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9782.868 - CS Toptec, bayable

Bayable, double-walled outdoor housing with 100 mm base, door, rear panel, and seamlessly bayable weatherproof roof. The complete enclosure frame is available for efficient and flexible interior fitting. The housing is prepared for the installation of a wall-mounted cooling unit Blue e+ Outdoor.



## Features

|                 |  |
|-----------------|--|
| Model No.       | CS 9782.868  |
| Version         | For baying<br>With cut-out for outdoor climate control unit 5118.21 BTU/h  |
| Material        | Housing frame: Stainless steel 1.4301 (AISI 304)<br>Enclosure panels and base/plinth panels: Aluminum, AlMg3<br>Rain canopy: Aluminum  |
| Surface finish  | Powder-coated<br>UV-resistant pure polyester   |
| Color           | RAL 7035   |
| Supply includes | Bayable, double-walled outdoor housing<br>Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels<br>Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027<br>Rear panel<br>Rain canopy<br>Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 800 mm<br>Height: 1,600 mm<br>Depth: 800 mm  |
| Dimensions                          | Overall height: 1,745 mm<br>Rain canopy height: 45 mm<br>Height of base/plinth: 100 mm  |
| Number of doors                     | 1   |
| Lock                                | Lock version: 3-point locking<br>No. of locks: 1<br>Lock Insert: BJ20027  |
| Gland plate                         | Size: 2<br>Qty.: 2  |
| Protection category IP to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 3R<br>NEMA 12  |
| IK code                             | IK10  |
| Note                                | All enclosure panels are double wall and grounded (external wall to internal wall)<br>For the assembly of an enclosure, side panels for CS Toptec, bayable are required |
| Note on Model No.:                  | To close the cutout, a climate control unit or adapter plate is needed  |
| Packaging unit                      | 1 pc(s).  |
| Net weight                          | 75 kg   |
| Gross weight                        | 75.5 kg   |
| Customs tariff number               | 94032080  |
| ETIM 9                              | EC000261  |
| ETIM 8                              | EC000261  |
| ECLASS 8.0                          | 27180101  |
| Product description                 | CS Toptec, bayable, WHD: 800x1600x800 mm, with breakout for outdoor climate control unit 1.5 kW   |

# Approvals

---

Explanations

Declaration of conformity