

# Rittal – The System.

Faster – better – everywhere.



## CS 9888.560

## CS Toptec

State: 2025-07-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9888.560 - CS Toptec

Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.



## Features

Model No.	CS 9888.560
Version	With cut-out for outdoor climate control unit 6824.28 - 17060.71 BTU/h
Product description	Outdoor enclosure with 100 mm transport base/plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS8 frame is available for interior installation.
Material	Housing frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth panels: Aluminum, AlMg3 Rain canopy: Aluminum
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035

# Features

---

Supply includes	Double-walled outdoor housing, fully preconfigured Enclosure frame with 25 mm system perforation in roof and base frames as well as vertical profiles with 2 mounting levels Front door with door stay, swing lever handle and semi-cylinder, lock BJ20027 Side panels left and right Rear panel Rain canopy Base/plinth with screw-fastened flange plates and screw-fastened trim panels front and rear
Dimensions	Width: 800 mm Height: 1,800 mm Depth: 800 mm
Protection category IP to IEC 60529	IP 55
IK code	IK10
Note	All enclosure panels are double wall and grounded (external wall to internal wall) CS Toptec is the foundation for project solutions in the outdoor sector. It can be requested under these order numbers: For individual installations: 9774.099, for buying: 9774.005
Note on Model No.:	A climate control unit is needed to seal the cut-out
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	116
Gross weight	118
EAN	4028177981942
ETIM 9	EC000261
ECLASS 8.0	27180101

# Approvals

---

# Approvals

---

Explanations

Declaration of conformity