

# Rittal – The System.

Faster – better – everywhere.



## DK 9962.182

## Network/server enclosures TS IT

State: 2025-07-20 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 9962.182 - Network/server enclosures TS IT Dynaload with shock pallet

The TS IT Dynaload rack is built for integration and rapid deployment. Overall load capacity at 2500 lbs. Includes shock pallet and ramp.

## Features

Model No.	DK 9962.182
Product description	The TS IT Dynaload arrives on a special shock absorbing, torque preventing pallet, ready for build-out and rapid deployment.
Material	Carbon steel
Surface finish	Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005
Supply includes	Enclosure frame TS 8 with doors and roof plate Carbon steel door at the front, vented (free area in perforated carbon steel part approx. 85 %), 180° hinges Carbon steel door at rear, ventilated in one piece (free area in perforated carbon steel part approx. 85 %), 130° hinges Comfort handle (8611.200 lock) front and rear Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate Spacers to raise the fan cover plate, for passive cooling (supplied loose) Grounding accessories (supplied loose) Captive nuts, M6, conductive (supplied loose) Preinstalled heavy-duty casters Shock pallet and ramp, with transportation brackets
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,200 mm
Installation height for components	42 U

# Features

Load capacity of the 19" levels	1,134 kg
Packaging unit	1 pc(s).
Net weight	528.99
Gross weight	528.99
UPC-Code	88429

# Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------