

# Rittal – The System.

Faster – better – everywhere.



## RX 9364.022

## RiLineX bus-mounting fuse base

状态: 2025-10-11 (来源: [rittal.com/cn-zh](http://rittal.com/cn-zh))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9364.022 - RiLineX bus-mounting fuse base

Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylinder lock 10 x 38 mm with optical LED fuse monitoring. For reliable contacting of the cylindrical fuses, the device features special fuse holders which are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 16 mm<sup>2</sup> at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



## 特征

型号	RX 9364.022
您的获益	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm <sup>2</sup> Complete contact hazard protection without any additional accessories (such as screw caps)
材料	聚酰胺 (PA 6) 防火性能符合 UL 94-V0
颜色	RAL 35745 RAL 9005
导线出线	下面

# 特征

极数	3 极
适合于母线系统	RiLineX RiLine60
尺寸	宽度: 18 mm 高度: 263 mm 深度: 123.5 mm
圆导线连接, 细线带电缆芯线套管	1.5 - 6 mm <sup>2</sup>
连接圆导线, 细绞线, 带 AWG 冷压端头	AWG 16 - AWG 10
圆导线连接, 多芯	1.5 - 6 mm <sup>2</sup>
连接圆导线, 多股 (AWG 标准)	AWG 16 - AWG 10
适合于母线	15 x 5/10 20 x 5/10 30 x 5/10
额定电压	400 V AC
过压类别	4
污染等级	3
标准	IEC/DIN EN 60 947-3
Rated insulation voltage	800 V
Power dissipation (max.)	3 W
防护等级 IP, 符合 IEC 60 529 标准	IP 2XB
Operation humidity max	90 %
工作温度范围	-5 °C...55 °C
贮存温度范围	-25 °C...75 °C
空气湿度 (没有凝露)	10...90 %

# 特征

Utilisation category	AC-20B (400 V/100 A)
保险器熔丝	10 x 38 mm
包装单元	4 件
净重	1.008
毛重	1.014
铜成分 (kg/件)	0.043
税率号	85369095
ETIM 9	EC001644

# 批准

解释	符合性声明
----	-------