Rittal – The System.

Faster – better – everywhere.



# KL 1503.510

# Terminal boxes KL

State: 02/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# KL 1503.510 - Terminal boxes KL without gland plate

Spray-finished enclosure with sheet steel cover, without gland plate Protection category IP 66.

## Features

| | |
|---|---|
| Model No. | KL 1503.510 |
| Material | Enclosure: Sheet steel<br>Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover<br>Quick-release fastener including plastic bushes |
| Dimensions | Width: 300 mm<br>Height: 200 mm<br>Depth: 120 mm |
| Protection category to IEC 60 529 | IP 66 |
| Protection category NEMA | NEMA 4 |
| IK Code | IK08 |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 2.673 kg |
| Gross weight | 2.873 kg |
| Customs tariff number | 84879059 |
| ECLASS 8.0 | 27180101 |
| Product description | KL Terminal box, WHD: 300x200x120 mm, Sheet steel, without mounting plate, with cover, without gland plate |

© Rittal 2026

# Approvals

| | |
|---|---|
| Approvals | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Manufacturer's declaration<br>Declaration of conformity<br>Declaration of conformity UK |

# Tender text

Terminal box without gland plate (120 mm deep), protection cat. IP 66
Enclosure:
sturdy sheet steel construction, folded and welded from a single piece, with all-round protection channel on the
cover aperture, rear panel with recessed holes for wall mounting brackets, cover of sheet steel, sealed, with a highly
elastic, foamed-in special seal, facilities for connecting PE conductors in the cover and box, profile strips on both internal sides with mounting holes. Special plastic bush guards against accidental loss of the cover screws and provides screwdriver guidance.
Accessories:
quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate
Surface finish:
steel is cleaned, degreased, phosphated, electrophoretic dipcoat primed and electrostatically polyester powder-coated in textured RAL 7035
Dimensions (W x H x D): 300 x 200 x 120 mm