


Rittal – The System.

Faster – better – everywhere.



DK 2094.400 Slot-in cable gland, 482.6 mm (19")

State: 22/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 2094.400 - Slot-in cable gland, 482.6 mm (19")

Consists of an expanding nut which is inserted into the square attachment hole at the front and then secured with the assembly screw.



Features

| | |
|---------------------|--|
| Model No. | DK 2094.400 |
| Design | Size of mounting hole 9.5 x 9.5 mm |
| Product description | The cage nut consists of an expanding nut which is simply inserted into the square attachment hole at the front and then secured with the assembly screw. When tightening the screw, the cage expands and thus secures the required components. Clamping range from 1.2 – 4.5 mm. Multi-tooth screw head, bit size T 30. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Pan-head screws Expanding nuts Plastic washers |
| Dimensions | Thread: M6 Thread length: 16 mm |
| Packs of | 50 pc(s). |

Features

| | |
|-------------------------------|--|
| Net weight | 0.3 kg |
| Gross weight | 0.38 kg |
| PCF per pack (cradle-to-gate) | 1.3 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73181900 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |
| Product description | DK Slot-in cable gland, 482.6 mm (19"), M6, L: 16 mm |