# Rittal - The System.

Faster - better - everywhere.





# BG 1558.010 Bus enclosures BG

State: 17/11/2025 (Source: rittal.com/com-en)



## BG 1558.010 - Bus enclosures BG Stainless steel

Stainless steel bus enclosures 1.4301 (AISI 304), incl. 180° hinge. Protection category IP 66.

#### **Features**

Model No.	BG 1558.010
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea 180° hinges: Die-cast zinc
Surface finish	Enclosure and cover: Brushed, grain 240 180° hinges: chrome-plated
Supply includes	Enclosure with cover 180° hinges (2) Support rail TH 35/7.5 Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
Dimensions	Width: 400 mm Height: 200 mm Depth: 123 mm
Material thickness - enclosure	1.5 mm
Material thickness - door	1.25 mm
Door hinge position	bottom
Number of support rails	1
Lock	Lock version: Quick-release fastener including plastic bushes Number of locks: 2
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	3.92
Gross weight	4.12
Customs tariff number	94032080

© Rittal 2025

## Features

EAN	4028177009912
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

## **Approvals**

Approvals	Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3