### Rittal - The System.

Faster – better – everywhere.





## SK 3179.801 Blue e+ S wall-mounted cooling unit

State: 22/11/2025 (Source: rittal.com/com-en)



# SK 3179.801 - Blue e+ S wall-mounted cooling unit 0.3 kW - 1 kW

Blue e+ S cooling units with tried-and-tested Blue e+ technology are the world's most energy-efficient cooling units. This means they reduce the carbon footprint of your machines and systems. Available in a brand new design with a host of smart functions.



#### **Features**

Model No.	SK 3179.801
IVIOUEI INO.	31/3.001
Design	wall-mounted
Benefits	Contributes to climate-neutral production with average energy savings of 75% and a reduced carbon footprint
	Multi-voltage capabilities and country-specific approvals support
	global usability
	Smart, simple monitoring via IoT interface
	User-friendly operation with the Rittal Scan & Service app
Material	Sheet steel
General colour	RAL 7035
Colour	Enclosure: RAL 7035
	Louvred grille: RAL 7012
Supply includes	Assembly parts
	Fully wired ready for connection (plug-in terminal strip)
Options	For remote monitoring and networking of cooling units and chillers
	in the Blue e+ generation, please use the IoT interface (Model No.
	3124.300). Increase machine availability and process reliability with
	remote monitoring of device data, statuses and system messages.
	• • •

© Rittal 2025 2

#### **Features**

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.52 kW Cooling output L35 L35/60 Hz: 0.52 kW Cooling output L35 L50/50 Hz: 0.32 kW Cooling output L35 L50/60 Hz: 0.32 kW
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Note	Please observe the mounting instructions.  By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions.  Only suitable for use in semi-outdoor areas (see instructions for description)
Note on Model No.	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V)
Rated power input	0.36 kW
Air throughput (unimpeded air flow)	External circuit: 366.6 m³/h Internal circuit: 366.6 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.03 Refrigeration factor L35 L35 (EER) 60 Hz: 2.03
Design	wall-mounted
Dimensions	Width: 300 mm Height: 570 mm Depth: 199 mm
Required mounting cut-out	Cut-out width: 280 mm Cut-out height: 550 mm
Protection category to IEC 60 529	Internal circuit IP 55
Protection category NEMA	
	UL Type 12 UL Type 3R
Refrigerant/cooling medium	• •
	UL Type 3R  Refrigerant: R-513A  Quantity: 0.16 kg Global Warming Potential (GWP): 631
Refrigerant/cooling medium	UL Type 3R  Refrigerant: R-513A  Quantity: 0.16 kg  Global Warming Potential (GWP): 631  CO2 equivalent (CO2e): 0.1 t

© Rittal 2025

3

#### Features

Operating temperature range of refrigerant circuit (active)	3 °C60 °C
Heat pipe operating temperature range	-20 °C45 °C
Setting range	20 °C50 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.26 kW Power consumption L35 L35/60 Hz: 0.26 kW Power consumption L35 L50/50 Hz: 0.31 kW Power consumption L35 L50/60 Hz: 0.31 kW
Permissible operating pressure (p. max.)	32 bar
Packs of	1 pc(s).
Net weight	12.84
Gross weight	13.84
Customs tariff number	84158200
EAN	4028177962569
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

## Approvals

Approvals	30 - KC Korea
	UL + C-UL (listed)
	UL + C-UL - FTTA
Explanations	Declaration of conformity
	Declaration of conformity - F-gas regulation

© Rittal 2025 4