


Rittal – The System.

Faster – better – everywhere.



SZ 2411.671

Cable gland, polyamide

State: 08/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.671 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.671
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 53 mm
Thread	M63 x 1.5
Thread length	18 mm
Min. cable diameter	34 mm
Max. cable diameter	44 mm
Operating temperature range	-30 °C...100 °C
torque	25 Nm
Width across flats	65 mm
Dimensions	Thread: M63 x 1.5 Thread length: 18 mm
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	3 pc(s).

Features

Net weight	0.372 kg
Gross weight	0.375 kg
Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, polyamide, size: M63x1,5, for cables ø 34-44 mm

Approvals

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK
