


**Rittal – The System.**

Faster – better – everywhere.



# SZ 2411.871

## Cable gland, brass

State: 08/07/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.871 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SZ 2411.871  |
| Benefits                            | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.<br>Clamping membranes for even tightening and strain relief to protect the cables |
| Material                            | Brass<br>Seal: CR/NBR  |
| Surface finish                      | Nickel-plated  |
| IP protection category to IEC 60529 | IP 68 (5 bar, 30 min)  |
| Dimensions                          | Height: 54 mm  |
| Thread                              | M63 x 1.5  |
| Thread length                       | 14 mm  |
| Min. cable diameter                 | 34 mm  |
| Max. cable diameter                 | 44 mm  |
| Operating temperature range         | -40 °C...100 °C  |
| torque                              | 50 Nm  |
| Width across flats                  | 64 mm  |
| Dimensions                          | Thread: M63 x 1.5<br>Thread length: 14 mm  |
| Type rating to UL 50E               | Type 1<br>Type 4<br>Type 4X<br>Type 12<br>Type 13  |
| Packs of                            | 1 pc(s).   |

# Features

---

|                       |   |
|-----------------------|---|
| Net weight            | 0.48 kg   |
| Gross weight          | 0.498 kg  |
| Customs tariff number | 74198090  |
| ETIM 9                | EC000441  |
| ETIM 8                | EC000441  |
| ECLASS 8.0            | 27149109  |
| Product description   | SZ Cable gland, brass, size: M63x1,5, for cables ø 34-44 mm |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)<br>VDE                                 |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |