

Rittal – The System.

Faster – better – everywhere.



SZ 2482.600 Interface flap

State: 13/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2482.600 - Interface flap for RC circuit-breaker

According to standard EN 60 204-1, all circuits with a rated current of ≤ 20 A that supply sockets in or on machine enclosures must be fused with a residual-current circuit-breaker with a rated differential current of ≤ 30 mA. Prepared for the installation of standard, 2-pole RCBO circuit-breakers.

Features

| | |
|---------------------|---|
| Model No. | SZ 2482.600 |
| Design | Spring-action terminals max. 2 x 2.5 mm, connection at rear |
| Product description | According to standard EN 60 204-1, all circuits with a rated current of ≤ 20 A that supply sockets in or on machine enclosures must be fused with a residual-current circuit-breaker with a rated differential current of ≤ 30 mA. Prepared for the installation of standard, 2-pole RCBO circuit-breakers. |
| Benefits | Protection against fault currents and overload Standard-compliant fuse to EN 60 204 The RC switch may be reset without opening the enclosure Spring mechanism raises the unlocked cover by 30°. This ensures that you do not forget to close the cover. |
| Applications | As programming interface for controllers As maintenance access for networks For temporary connection of additional equipment For quick connection to existing network structures For programming and maintenance of integral components |
| Function principle | A snap fastener ensures reliable sealing. This may be locked if required. |
| Material | Mounting frame: Plastic PBT (black) Plastic flap: Polycarbonate (semi-transparent) |
| Supply includes | Interface flap, complete, consisting of plastic frame, socket (VDE), RJ 45 (jack/jack, Cat 5e) and cut-out for RC circuit-breaker Knockout provided for USB A (jack/jack) 3 mm double-bit with slot-in rotary knob |
| Mounting cut-out | Cut-out width: 117 mm Cut-out height: 91 mm |

Features

| | |
|-------------------------------------|---|
| Note | Interface flap may only be used with fitted RC circuit-breaker |
| Dimensions | Width: 131 mm Height: 127 mm |
| Rated operating voltage | 250 V, 1~, 50 Hz/60 Hz |
| Rated current 230 V, 50 Hz | 10 - 16 A |
| IP protection category to IEC 60529 | IP 65 |
| Packs of | 1 pc(s). |
| Net weight | 0.56 kg |
| Gross weight | 0.569 kg |
| Customs tariff number | 85366990 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Interface flap, complete, mounting frame and interface inserts, with plastic flap, semi-transparent, RJ45, sockel modules Germany, knock-out for RDC protective switch |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|