# Rittal - The System.

Faster – better – everywhere.





# SK 3238.500 TopTherm filter fans

State: 08/12/2025 (Source: rittal.com/com-en)



## SK 3238.500 - TopTherm filter fans with EC technology

Energy-efficient version of the RTT fan-and-filter units with EC technology. From 180  $\,\mathrm{m}^3$ /h with integral control interface (0-10 V / PWM input and tachosignal output) to regulate and monitor the fan.

#### **Features**

Model No.	SK 3238.500		
Design	wall-mounted EC		
Product description	Energy-efficient version of the TopTherm fan-and-filter units with diagonal fan technology. For controlling and monitoring fans 3240.50x to 3245.51x. The fan may be activated via the control interface with tacho signal output integrated as standard, and monitoring of the fan speed and function is supported.		
Product modification	The cover for the connection clamp has not been part of the TopTherm filter fans since May 2024. In testing, it proved not to be necessary to meet the standard, and affects neither function nor operational reliability.		
Colour	RAL 7035		
Supply includes	Complete unit ready to install, including chopped-fibre filter mat		
Fan	Diagonal, EC motor		
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 52 m³/h At 60 Hz: 52 m³/h		
Air throughput, unimpeded airflow (with pleated filter)	At 50 Hz: 63 m³/h At 60 Hz: 70 m³/h		
Air throughput with outlet filter including chopped-fibre filter mat (quantity x order number)	1 x 3238200: 36 m³/h 2 x 3238200: 46 m³/h		
Rated operating voltage	200 V - 240 V, 1~, 50 Hz/60 Hz		
Power consumption Pel	At 50 Hz: 5.8 W At 60 Hz: 5.8 W		

© Rittal 2025 2

### Features

Rated current max.	At 50 Hz: 0.045 A At 60 Hz: 0.045 A		
Dimensions	Width: 148.5 mm Height: 148.5 mm		
Installation depth	58.5 mm		
Mounting cut-out	Cut-out width: 124 mm Cut-out height: 124 mm		
IP protection category to IEC 60 529	IP 54 with chopped-fibre filter/pleated filter IP 56 with chopped-fibre filter/pleated filter and hose-proof hood		
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood		
Pre-fuse	Miniature circuit-breaker/fuse: 6 A		
Note	To increase the air throughput, a pleated filter may optionally be used (see characteristic curve). Suitable for use with fan-and-filter units, roof-mounted fans and outlet filters.  For even more efficient operation or for monitoring the filter fans, we recommend the use of the EC speed control for EC filter fans (from an air throughput of 180 m³/h).		
Operating temperature range	-20 °C55 °C		
Storage temperature range	-30 °C70 °C		
Noise level	At 50 Hz: 49 dB(A) At 60 Hz: 49 dB(A)		
Packs of	1 pc(s).		
Net weight	0.5		
Gross weight	0.625		
Customs tariff number	84145915		
EAN	4028177664128		
ETIM 9	EC000320		
ETIM 8	EC000320		

© Rittal 2025 3

### **Features**

CLASS 8.0	27180716

## **Approvals**

Approvals	CSA
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025

#### Tender text

TopTherm fan-and-filter units with EC technology

Energy-efficient version of the

TopTherm fan-and-filter units with diagonal fan technology.

Fans 3240.500 to 3245.510 may be controlled and monitored.

The fan may be activated via the control interface

with tacho signal output integrated as standard,

and monitoring of the fan speed and function is supported.

Air troughput (unimpeded air flow): 52 m3/h

Power consumption 50/60 Hz: 6,1 / 6,1 W

Rated power input 50/60 Hz: 0,045 / 0,045 A

Rated operating voltage: 200-240 V, 1~, 50/60 Hz

Diagonal fan: Diagonal, EC motor

Dimensions [WxH]: 148,5x148,5 mm

Installation depth: 58,5 mm

Build depth: 16 mm

Required mounting cut-out [WxH]: 124x124 mm

Operating temperature range: -20 °C to 55 °C

Storage temperature range: -30 °C to 70 °C

Colour: RAL 7035

Protection category IP to IEC 60 529:

IP 54 with fleece filter/pleated filter

IP 56 with fleece filter/pleated filter and hose-proof hood

Protection category NEMA:

Type 12 with fleece filter/pleated filter

Type 3, 3R, 4, 4X with fleece filter/pleated filter and hose-proof hood

Noise level 50/60 Hz: 49 / 49 dB(A)

Service life 50/60 Hz: 62.500 h

Weight: 0,62 kg

© Rittal 2025 5