

Rittal – The System.

Faster – better – everywhere.



SK 3126.115

TopTherm air-air heat exchanger

State: 14/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3126.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

Model No.	SK 3126.115
Design	wall-mounted
Product description	Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another.
Colour	RAL 7035
Supply includes	Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Assembly parts
Specific thermal output	17.5 W/K
Air throughput (unimpeded air flow)	External circuit with 50 Hz: 265 m ³ /h External circuit with 60 Hz: 315 m ³ /h Internal circuit at 50 Hz: 265 m ³ /h Internal circuit at 60 Hz: 315 m ³ /h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.46 A At 60 Hz: 0.5 A
Dimensions	Width: 280 mm Height: 550 mm Depth: 150 mm
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Temperature control	Electronic control with digital display (factory setting +35 °C)
Operating temperature range	-5 °C...55 °C

Features

IP protection category to IEC 60529	Internal circuit IP 54 External circuit IP 34
Packs of	1 pc(s).
Net weight	8.94 kg
Gross weight	9.54 kg
Customs tariff number	84158300
ETIM 9	EC002514
ETIM 8	EC002514
ECLASS 8.0	27180711
Product description	SK TopTherm air/air heat exchanger, wall-mounted, 17.5 W/K, 115V, 50/60Hz, WHD: 280 x 550 x 150 mm

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK