


Rittal – The System.

Faster – better – everywhere.



SK 3179.801

Blue e+ S wall-mounted cooling unit

State: 13/01/2026 (Source: rittal.com/com-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3179.801 - Blue e+ S wall-mounted cooling unit 0.3 kW – 1 kW

Blue e+ S cooling units with tried-and-tested Blue e+ technology are the world's most energy-efficient cooling units. This means they reduce the carbon footprint of your machines and systems. Available in a brand new design with a host of smart functions.



Features

Model No.	SK 3179.801
Design	wall-mounted
Benefits	Contributes to climate-neutral production with average energy savings of 75% and a reduced carbon footprint Multi-voltage capabilities and country-specific approvals support global usability Smart, simple monitoring via IoT interface User-friendly operation with the Rittal Scan & Service app
Material	Sheet steel
General colour	RAL 7035
Colour	Enclosure: RAL 7035 Louvre grille: RAL 7012
Supply includes	Assembly parts Fully wired ready for connection (plug-in terminal strip)
Options	For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages.

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.52 kW Cooling output L35 L35/60 Hz: 0.52 kW Cooling output L35 L50/50 Hz: 0.32 kW Cooling output L35 L50/60 Hz: 0.32 kW
Rated operating voltage	110 V - 240 V, 1~, 50 Hz/60 Hz
Note	<p>Please observe the mounting instructions.</p> <p>By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions.</p> <p>Only suitable for use in semi-outdoor areas (see instructions for description)</p>
Note on Model No.	Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V)
Rated power input	0.36 kW
Air throughput (unimpeded air flow)	External circuit: 366.6 m ³ /h Internal circuit: 366.6 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.03 Refrigeration factor L35 L35 (EER) 60 Hz: 2.03
Design	wall-mounted
Dimensions	Width: 300 mm Height: 570 mm Depth: 199 mm
Required mounting cut-out	Cut-out width: 280 mm Cut-out height: 550 mm
Protection category to IEC 60 529	Internal circuit IP 55
Protection category NEMA	UL Type 12 UL Type 3R
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.16 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.1 t
Temperature control	e+ controller (factory setting +35 °C)
Operating temperature range	-20 °C...60 °C
Storage temperature range	-40 °C...70 °C

Features

Operating temperature range of refrigerant circuit (active)	3 °C...60 °C
Heat pipe operating temperature range	-20 °C...45 °C
Setting range	20 °C...50 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.26 kW Power consumption L35 L35/60 Hz: 0.26 kW Power consumption L35 L50/50 Hz: 0.31 kW Power consumption L35 L50/60 Hz: 0.31 kW
Permissible operating pressure (p. max.)	32 bar
Packs of	1 pc(s).
Net weight	12.84
Gross weight	13.84
Customs tariff number	84158200
EAN	4028177962569
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation
